



Clamp DIN 32676 A

| DN | A | B | C | D | E1 | E2 |
|----|------|----|----|------|------|------|
| 25 | 50,5 | 26 | 29 | 21,5 | 53,0 | 50,0 |
| 32 | 50,5 | 32 | 35 | 21,5 | 53,0 | 50,0 |
| 40 | 50,5 | 38 | 41 | 21,5 | 53,0 | 50,0 |
| 50 | 64,0 | 50 | 53 | 21,5 | 66,0 | 63,0 |

Clamp ISO (DIN 32676 B)

| DN/OD | A | B | C | D | E1 | E2 |
|-------|------|------|------|------|------|------|
| 21,3 | 50,5 | 18,1 | 21,3 | 21,5 | 53,0 | 50,0 |
| 26,9 | 50,5 | 23,7 | 26,9 | 21,5 | 53,0 | 50,0 |
| 33,7 | 50,5 | 29,7 | 33,7 | 21,5 | 53,0 | 50,0 |
| 42,4 | 64,0 | 38,4 | 42,4 | 21,5 | 66,0 | 63,0 |
| 48,3 | 64,0 | 44,3 | 48,3 | 21,5 | 66,0 | 63,0 |

Clamp en pouces (DIN 32676 C)

| Size | A | B | C | D | E1 | E2 |
|------|------|------|------|------|------|------|
| 1" | 50,5 | 22,1 | 25,4 | 21,5 | 53,0 | 50,0 |
| 1,5" | 50,5 | 34,8 | 38,1 | 21,5 | 53,0 | 50,0 |
| 2" | 64,0 | 47,5 | 50,8 | 21,5 | 66,0 | 63,0 |

HELYON

5 chemin du Jubin

F-69570 DARDILLY

Tél. +33-(0)4 72 52 16 70

e-mail: contact@helyon.com

DISQUE DE RUPTURE PLAT NON FRAGMENTANT

Montage directement entre clamps

DN 25 à DN 50 / DN/OD 21,3 à 48,3 / Size 1" à 2"